

HIGH IMPACT MAGNETIC CONTACTS

0E-DC1651W10
PRESS FIT
MAGNETIC CONTACT



High Impact means , no loss of performance due to adverse stress caused by building movement, sudden impacts, or temperature change.

SPECIFICATIONS

Diameter	0.375"
Height	0.28125"
Wire Leads	12" AWG#22
Max. Contact Rating	30VDC, 0.2A, 5W
Loop Type	Closed
Reed Form	N/O
Closed Gap	0.75" (19mm)
Departure Gap	0.8" (20mm)
Max. Initial Contact Resistance	0.150 Ω

PART #: 0E-DC1651W10

UPC: 811914020066

Crush Resistant

Simple Installation

Durable Magnet

Product Certification:

