

PLUG-IN TRANSFORMER

0E-PPS2440
24VAC, 40VA
AUTO-RESETTING PTC FUSE



The 0E-PPS2440 is a plug-in 24VAC, 40VA plug-in transformer that provides reliable AC power for a wide variety of indoor security and surveillance products and applications. It is auto-resetting PTC fuse protected and includes a power indicator LED. Grounding is provided via a third screw terminal and ground plug. Complies with DOE Level VI Efficiency requirements for alarm industry plug-in power supplies.

- 24VAC, 40VA (40 WATTS)
- PRIMARY: 120VAC, 60Hz, 50W
- CLASS 2
- AUTO-RESETTING PTC FUSE PROTECTED
- POWER INDICATOR LED
- 3 SCREW TERMINALS AND GROUNDING PLUG
- EFFICIENCY LEVEL VI COMPLIANT AND UL LISTED
- FOR INDOOR USE ONLY
- OPERATING TEMP.: 23°F to 86°F (-5°C to 30°C)

PART #: 0E-PPS2440
UPC: 811914025719
LENGTH: 2.2"
WIDTH: 2.6"
HEIGHT: 4.1"
WEIGHT: 1 LB., 9 OUNCES



**FOR MORE INFORMATION,
CONTACT YOUR ADI SALES PERSON.**

wboxtech.com