

## HIGH IMPACT MAGNETIC CONTACTS

0E-ROPLUNGE  
ROLLER BALL/PLUNGER



High Impact means , no loss of performance due to adverse stress caused by building movement, sudden impacts, or temperature change.

### SPECIFICATIONS

<b>Diameter</b>	3/4"
<b>Wire Leads</b>	12" AWG#22
<b>Max. Contact Rating</b>	30VDC, 0.2A, 5W
<b>Loop Type</b>	Closed
<b>Reed Form</b>	N/O
<b>Closed Gap</b>	0.25" (6mm)
<b>Max. Initial Contact Resistance</b>	0.150 $\Omega$

PART #: 0E-ROPLUNGE

UPC: 811914026263

Flush Mount

Screw down flange

Simple Installation

Spacer and Mounting

Hardware included

Product Certification:

