SPEC SHEET



BATTERY BACK UP 2,000VA / 1540W LINE INTERACTIVE UPS

0E-RCKMT2200 COMMERCIAL LINE-INTERACTIVE **RACK/TOWER UPS**



The OE-RCKMT2200 Uninterruptable Power Supply (UPS) is ideal for servers, telecom, network, and security equipment. With 2,000VA and 1540 Watts of capacity, the 0E-RCKMT2200 UPS protects equipment from blackouts, brown outs, spikes, and surges.

- AUTOMATIC VOLTAGE REGULATION (AVR)
- 2.000VA / 1540W CAPACITY
- 120V NOMINAL VOLTAGE
- I CD DISPLAY
- ENERGY STAR QUALIFIED
- 8 STANDARD GROUNDED OUTLETS (BATTERY / SURGE PROTECTED)
- TRANSFER TIME 4ms
- FREE MANAGEMENT SOFTWARE DOWNLOAD
- 1,470 JOULES OF SURGE PROTECTION
- 2U RACK / TOWER CONVERTIBLE CHASSIS
- RACKMOUNT EARS
- CONNECTED EQUIPMENT WARRANTY \$300,000

0E-RCKTMT2200 PART #:

UPC: 8 40049 30122 1

I FNGTH: 15.3" WIDTH: 17"

HEIGHT: 3.5"

WFIGHT: 57.2 LBS

FULL-LOAD RUNTIME: 4.5 MIN HAI F-I OAD RUNTIMF: 15.5 MIN BATTERY SIZE: 12V / 9Ah

UI I ISTING: **E473223**

Product Certification:







