## **SPEC SHEET**



## **BATTERY BACK UP 700VA / 400W** LINE INTERACTIVE UPS

0E-RCKMT700 **COMMERCIAL** LINE-INTERACTIVE **RACK/TOWER UPS** 



The OE-RCKMT700 Uninterruptable Power Supply (UPS) is ideal for servers, telecom, network, and security equipment. With 700VA and 400 Watts of capacity, the 0E-RCKMT700 UPS protects equipment from blackouts, brown outs, spikes, and surges.

- AUTOMATIC VOLTAGE REGULATION (AVR)
- 700VA / 400W CAPACITY
- 120V NOMINAL VOLTAGE
- I CD DISPLAY
- FNERGY STAR QUALIFIED
- 6 STANDARD GROUNDED OUTLETS (4 BATTERY / SURGE PROTECTED 2 SURGE PROTECTED ONLY)
- TRANSFER TIME 4ms
- FREE MANAGEMENT SOFTWARE DOWNLOAD
- 1.150 JOULES OF SURGE PROTECTION
- 1U RACK MOUNT CHASSIS
- RACKMOUNT EARS.
- CONNECTED EQUIPMENT WARRANTY \$300,000

PART #: 0E-RCKMT700

UPC: 8 40049 30123 8

LENGTH: 9.25" WIDTH: 17.05" HEIGHT: 1.75"

WFIGHT: 18.5 LBS

FULL-LOAD RUNTIME: 3 MIN HAI F-I OAD RUNTIME: **11 MIN** BATTERY SIZE: 6V / 8Ah

UI I ISTING: **E473223** 

Product Certification:







