



5MP IP IR Motorized Dome

2560x1920 TRUE DAY/NIGHT



The R2-5MPDMTRZ is a 5MP (2560 x 1920) IP67 rated dome camera constructed with a 2.7-13.5mm lens and provides HD Image quality.

OPTIONAL SERVICES*

Integrate with Capture Cloud Service, powered by Eagle Eye*

Connect with Capture Remote Monitoring Service (R2-B12SUBK)*

**Require monthly/annual subscriptions*

FEATURES

- 2.7-13.5MM LENS
- IR DISTANCE: 40M/131FT
- SUPPORTS MICRO SD CARD, UP TO 256GB
- TRUE WDR
- ONVIF CONFORMANCE
- IP67/IK10
- POE/12VDC
- WARRANTY: 36 MONTHS
- PART #: R2-5MPDMTRZ
- UPC: 840049305281
- LENGTH: Φ 5.12" \times 4.41"
- WEIGHT: 1.76 LB



FOR MORE INFORMATION, CONTACT YOUR ADI SALES PERSON.

Capture

▶▶▶▶▶ advance

PRODUCT SPEC SHEET
R2-5MPDMTRZ

Caméra Dôme Motorisée IP IR 5 Mpx



JOUR/NUIT AUTHENTIQUE 2560 x 1920

Le modèle R2-5MPDMTRZ est un camera dôme 5 Mpx (2560 x 1920) certifiée IP67 dotée d'un objectif de 2,7 - 13,5 mm et offrant une qualité d'image HD.

SERVICES EN OPTION*

Intégrez-vous à Capture Cloud Service, optimisé par Eagle Eye.*

Connexion aux services de surveillance à distance de Capture (R2-B12SUBK)*

**Nécessite un abonnement mensuel ou annuel*

FEATURES

- OBJECTIF DE 2,7 - 13.5 MM
- DISTANCE (IR) : 40 M/131 PI
- PRISE EN CHARGE DES CARTES MICRO SD JUSQU'À 256 GO
- PLAGES DYNAMIQUES ÉTENDUES
- CONFORMITÉ ONVIF
- IP67/IK10
- POE/12 VCC
- GARANTIE : 36 MOIS
- PART #: R2-5MPDMTRZ
- UPC: 840049305281
- LENGTH: Φ 5.12" × 4.41"
- WEIGHT: 1.76 LB



FOR MORE INFORMATION, CONTACT YOUR ADI SALES PERSON.

CAMERA

IMAGE SENSOR	1/2.8" PROGRESSIVE SCAN CMOS
EFFECTIVE PIXELS	2560(H)×1920(V)
ELECTRONIC SHUTTER	AUTO/MANUAL, 1/5 - 1/20,000S
MIN. ILLUMINATION	Color: 0.03 Lux @ (F1.6, AGC ON) , B/W: 0 Lux @ (IR LED ON)
S/N RATIO	55DB
DAY/NIGHT	AUTO(ICR)/DAY/NIGHT/TIME
WIDE DYNAMIC RANGE	TRUE WDR
IR RANGE	UP TO 40 M (131 FT)
IR ON/OFF CONTROL	AUTO/MANUAL
PAN/TILT/ROTATION RANGE	PAN: 0° - 355°, TILT: 0° - 80°, ROTATION: 0° - 355°

LENS

LENS TYPE	MOTORIZED FOCUS
IRIS	FIXED IRIS
FOCAL LENGTH	2.7 - 13.5 MM
F NUMBER	F1.6
ANGLE OF VIEW	H: 87.5° - 26°, V: 64.8° - 19.9°

VIDEO

MAX. RESOLUTION	5MP (2560×1920)
STREAMING CAPABILITY	3 STREAMS
STREAM/FRAME RATE	STREAM1: 2560×1920, 2592×1520, 1920×1080, 1280×720 @ 25/30FPS STREAM2: D1, VGA, CIF @ 25/30FPS STREAM3: VGA, CIF, QVGA @25/30FPS
BIT RATE CONTROL	CBR/VBR
BIT RATE	STREAM1: 200kbps-12Mbps STREAM2: 100kbps-6Mbps STREAM3: 100kbps-3Mbps
IMAGE ENHANCEMENT	HLC / BLC / DEFOG / WDR
WHITE BALANCE	AUTO
GAIN CONTROL	AUTO/MANUAL
NOISE REDUCTION	2D/3D DNR
AISLE MODE	SUPPORTED
SMART IR	SUPPORTED
MIRROR	SUPPORTED
REGION OF INTEREST	OFF/ON (8 ZONE, RECTANGLE)
MOTION DETECTION	SUPPORTED
PRIVACY MASKING	SUPPORTED

SMART FUNCTION

SMART FUNCTION	SUPPORTS FACE, HUMAN, VEHICLE DETECTION AND CAPTURE
INTELLIGENT DETECTION	PERIMETER, SINGLE VIRTUAL FENCE, DOUBLE VIRTUAL FENCES, LOITER, PEOPLE COUNTING

AUDIO

COMPRESSION	G.711, RAW_PCM
BIT RATE	8KBPS, 16KPS, 64KBPS

NETWORK

PROTOCOLS	IPV4/IPV6, 802.1X, HTTP, HTTPS, TCP/IP, UDP/IP, RTSP, DHCP, NTP, RTCP/RTP, PPPOE, SMTP, DNS, UPNP, FTP, ARP, SNMP, TLS/SSL
INTEROPERABILITY	ONVIF, SDK, CGI
STREAMING METHOD	UNICAST
MAX. USER ACCESS	10 USERS
WEB VIEWER	<IE11, CHROME, FIREFOX, MICROSOFT EDGE
MANAGEMENT SOFTWARE	CAPTURE ADV

INTERFACE

ETHERNET	1 ETHERNET (10/100 BASE-T) RJ-45 CONNECTOR
AUDIO	1CH INPUT, 1CH OUTPUT
ALARM	1CH INPUT, 1CH OUTPUT
RESET BUTTON	SUPPORTED
STORAGE	BUILT-IN MICRO SD SLOT, UP TO 256G

ELECTRICAL

POWER SUPPLY	DC12V/POE (IEEE 802.3AF)
POWER CONSUMPTION	MAX 8.5 W
OPERATING TEMPERATURE	-40°C - 55°C (-40°F - 131°F)
OPERATING HUMIDITY	LESS THAN 90% RH
INGRESS PROTECTION	IP67, IK10
CERTIFICATIONS	CE/FCC
CASING	METAL
DIMENSIONS	Φ130 × 112MM (Φ5.12" × 4.41")
NET WEIGHT	0.8 KG (1.76 LB)

**FOR MORE INFORMATION,
CONTACT YOUR ADI SALES PERSON.**