

## 5MP IP IR Fixed Turret



2560x1920 TRUE DAY/NIGHT

The R2-5MPFXTUR is a 5MP (2560 x 1920) IP66 rated dome camera constructed with a 2.8mm lens and provides HD Image quality.

### OPTIONAL SERVICES\*

Integrate with Capture Cloud Service, powered by Eagle Eye\*

Connect with Capture Remote Monitoring Service (R2-B12SUBK)\*

*\*Require monthly/annual subscriptions*

## FEATURES

- 2.8MM LENS
- IR DISTANCE: 30M/98FT
- SUPPORTS MICRO SD CARD, UP TO 256GB
- TRUE WDR
- ONVIF CONFORMANCE
- IP66
- POE/12VDC
- WARRANTY: 36 MONTHS
- PART #: R2-5MPFXTUR
- UPC: 840049305267
- DIMENSION:  $\Phi$  4.65" x 3.7"
- WEIGHT: 1.21 LB



FOR MORE INFORMATION, CONTACT YOUR ADI SALES PERSON.

## Caméra Tourelle Fixe IP IR 5 Mpx



JOUR/NUIT AUTHENTIQUE 2592 x 1944

Le modèle R2-5MPFXTUR est un camera dôme 5 Mpx (2592 x 1944) certifiée IP66 dotée d'un objectif de 2.8 mm et offrant une qualité d'image HD.

### SERVICES EN OPTION\*

**Intégrez-vous à Capture Cloud Service, optimisé par Eagle Eye.\***

**Connexion aux services de surveillance à distance de Capture (R2-B12SUBK)\***

*\*Nécessite un abonnement mensuel ou annuel*

## FEATURES

- OBJECTIF DE 2,8 MM
- DISTANCE (IR) : 30 M/98 PI
- PRISE EN CHARGE DES CARTES MICRO SD JUSQU'À 256 GO
- PLAGES DYNAMIQUES ÉTENDUES
- CONFORMITÉ ONVIF
- IP66
- POE/12 VCC
- GARANTIE : 36 MOIS
- PART #: R2-5MPFXTUR
- UPC: 840049305267
- DIMENSION:  $\Phi$  4.65" x 3.7"
- WEIGHT: 1.21 LB



FOR MORE INFORMATION, CONTACT YOUR ADI SALES PERSON.

CAMERA	
IMAGE SENSOR	1/2.8" PROGRESSIVE SCAN CMOS
EFFECTIVE PIXELS	2592(H)×1944(V)
ELECTRONIC SHUTTER	AUTO/MANUAL, 1/5 - 1/20,000S
MIN. ILLUMINATION	COLOR: 0.05 LUX @ (F1.2, AGC ON) , B/W: 0 LUX @ (IR LED ON)
S/N RATIO	55DB
DAY/NIGHT	AUTO(ICR)
WIDE DYNAMIC RANGE	TRUE WDR
IR RANGE	UP TO 30 M (98 FT)
IR ON/OFF CONTROL	AUTO/MANUAL
PAN/TILT/ROTATION RANGE	PAN: 0° - 360°, TILT: 0° - 90°, ROTATION: 360°
LENS	
LENS TYPE	FIXED FOCUS
IRIS	FIXED IRIS
FOCAL LENGTH	2.8 MM (4 MM OPTIONAL)
F NUMBER	F2.0
ANGLE OF VIEW	H: 93.4°, V: 69.1°
VIDEO	
MAX. RESOLUTION	5MP (2592×1944)
STREAMING CAPABILITY	3 STREAMS
STREAM/FRAME RATE	STREAM1: 2560×1920, 2592×1520, 1920×1080, 1280×720 @ 25/30FPS STREAM2: D1, VGA, CIF @ 25/30FPS STREAM3: VGA, CIF, QVGA @25/30FPS
BIT RATE CONTROL	CBR/VBR
BIT RATE	STREAM1: 200KBPS-12MBPS STREAM2: 100KBPS-6MBPS STREAM3: 100KBPS-3MBPS
IMAGE ENHANCEMENT	HLC / BLC / DEFOG / WDR
WHITE BALANCE	AUTO
GAIN CONTROL	AUTO/MANUAL
NOISE REDUCTION	2D/3D DNR
AISLE MODE	SUPPORTED
SMART IR	SUPPORTED
MIRROR	SUPPORTED
REGION OF INTEREST	OFF/ON (8 ZONE, RECTANGLE)
MOTION DETECTION	SUPPORTED
PRIVACY MASKING	SUPPORTED

SMART FUNCTION	
SMART FUNCTION	SUPPORTS FACE, HUMAN, VEHICLE DETECTION
INTELLIGENT DETECTION	PERIMETER, SINGLE VIRTUAL FENCE, DOUBLE VIRTUAL, CONVERSE, PEOPLE COUNTING
AUDIO	
COMPRESSION	G.711, RAW_PCM
BIT RATE	8KBPS, 16KPS, 64KBPS
NETWORK	
PROTOCOLS	IPV4/IPV6, 802.1X, HTTP, HTTPS, TCP/IP, UDP/IP, RTSP, DHCP, NTP, RTCP/RTP, PPPOE, SMTP, DNS, UPNP, FTP, ARP, SNMP, TLS/SSL
INTEROPERABILITY	ONVIF, SDK, CGI
STREAMING METHOD	UNICAST
MAX. USER ACCESS	10 USERS
WEB VIEWER	<IE11, CHROME, FIREFOX, MICROSOFT EDGE
MANAGEMENT SOFTWARE	CAPTURE ADV
INTERFACE	
ETHERNET	1 ETHERNET (10/100 BASE-T) RJ-45 CONNECTOR
AUDIO	1CH INPUT, 1CH OUTPUT built-in Microphone
ALARM	1CH INPUT, 1CH OUTPUT
RESET BUTTON	SUPPORTED
STORAGE	BUILT-IN MICRO SD SLOT, UP TO 256G
ELECTRICAL	
POWER SUPPLY	DC12V/POE (IEEE 802.3AF)
POWER CONSUMPTION	MAX 7.5 W
OPERATING TEMPERATURE	-40°C - 55°C (-40°F - 131°F)
OPERATING HUMIDITY	LESS THAN 90% RH
INGRESS PROTECTION	IP66
CERTIFICATIONS	CE/FCC
CASING	METAL + PLASTIC
DIMENSIONS	Φ118 x 94MM (4.65" x 3.7")
NET WEIGHT	0.55 KG (1.04LB)

**FOR MORE INFORMATION,  
CONTACT YOUR ADI SALES PERSON.**