



PRODUCT SPEC SHEET  
R2-5MPTRMTRZ

# 5MP IP IR Motorized Turret

2560x1920 TRUE DAY/NIGHT



The R2-5MPTRMTRZ is a 5MP (2560 x 1920) IP66 rated turret camera constructed with a 2.7-13.5mm lens and provides HD Image quality.

## OPTIONAL SERVICES\*

Integrate with Capture Cloud Service, powered by Eagle Eye\*

Connect with Capture Remote Monitoring Service (R2-B12SUBK)\*

*\*Require monthly/annual subscriptions*

## FEATURES

- 2.7-13.5MM LENS
- IR DISTANCE: 40M/131FT
- SUPPORTS MICRO SD CARD, UP TO 256GB
- TRUE WDR
- ONVIF CONFORMANCE
- IP66
- POE/12VDC
- WARRANTY: 36 MONTHS
- PART #: R2-5MPTRMTRZ
- UPC: 840049305304
- DIMENSION:  $\Phi$  5.51 × 4.69"
- WEIGHT: 1.98 LB



FOR MORE INFORMATION, CONTACT YOUR ADI SALES PERSON.

# Caméra Tourelle Motorisée IP IR 5 Mpx



JOUR/NUIT AUTHENTIQUE 2560 x 1920GHT

Le modèle R2-5MPTRMTRZ est un camera tourelle 5 Mpx (2560 x 1920) certifiée IP66 dotée d'un objectif de 2,7 - 13,5 mm et offrant une qualité d'image HD.

**SERVICES EN OPTION\***

**Intégrez-vous à Capture Cloud Service, optimisé par Eagle Eye.\***

**Connexion aux services de surveillance à distance de Capture (R2-B12SUBK)\***

*\*Nécessite un abonnement mensuel ou annuel*

## FEATURES

- OBJECTIF DE 2,7 - 13,5 MM
- DISTANCE (IR) : 40 M/131 PI
- PRISE EN CHARGE DES CARTES MICRO SD JUSQU'À 256 GO
- PLAGES DYNAMIQUES ÉTENDUES
- CONFORMITÉ ONVIF
- IP66
- POE/12 VCC
- GARANTIE : 36 MOIS
- PART #: R2-5MPTRMTRZ
- UPC: 840049305304
- DIMENSION:  $\Phi 5.51 \times 4.69$ "
- WEIGHT: 1.98 LB



FOR MORE INFORMATION, CONTACT YOUR ADI SALES PERSON.

| CAMERA                         |  |
|--------------------------------|--|
| <b>IMAGE SENSOR</b>            | 1/2.8" PROGRESSIVE SCAN CMOS   |
| <b>EFFECTIVE PIXELS</b>        | 2560(H)×1920(V)  |
| <b>ELECTRONIC SHUTTER</b>      | AUTO/MANUAL, 1/5 - 1/20,000S   |
| <b>MIN. ILLUMINATION</b>       | COLOR: 0.03 LUX @ (F1.6, AGC ON) , B/W: 0 LUX @ (IR LED ON)  |
| <b>S/N RATIO</b>               | 55DB   |
| <b>DAY/NIGHT</b>               | AUTO(ICR)  |
| <b>WIDE DYNAMIC RANGE</b>      | TRUE WDR   |
| <b>IR RANGE</b>                | UP TO 40 M (131 FT)  |
| <b>IR ON/OFF CONTROL</b>       | AUTO/MANUAL  |
| <b>PAN/TILT/ROTATION RANGE</b> | PAN: 0° - 360° , TILT: 0° - 90° , ROTATION: 0° - 360°  |
| LENS                           |  |
| <b>LENS TYPE</b>               | MOTORIZED  |
| <b>IRIS</b>                    | FIXED IRIS   |
| <b>FOCAL LENGTH</b>            | 2.7 - 13.5 MM  |
| <b>F NUMBER</b>                | F1.6   |
| <b>ANGLE OF VIEW</b>           | H: 87.5° - 26° , V: 64.8° - 19.9°  |
| VIDEO                          |  |
| <b>MAX. RESOLUTION</b>         | 5MP (2560×1920)  |
| <b>STREAMING CAPABILITY</b>    | 3 STREAMS  |
| <b>STREAM/FRAME RATE</b>       | STREAM1: 2560×1920, 2592×1520, 1920×1080, 1280×720 @ 25/30FPS<br>STREAM2: D1, VGA, CIF @ 25/30FPS<br>STREAM3: VGA, CIF, QVGA @25/30FPS |
| <b>BIT RATE CONTROL</b>        | CBR/VBR  |
| <b>BIT RATE</b>                | STREAM1: 200KBPS-12MBPS<br>STREAM2: 100KBPS-6MBPS<br>STREAM3: 100KBPS-3MBPS  |
| <b>IMAGE ENHANCEMENT</b>       | HLC / BLC / DEFOG / WDR  |
| <b>WHITE BALANCE</b>           | AUTO   |
| <b>GAIN CONTROL</b>            | AUTO/MANUAL  |
| <b>NOISE REDUCTION</b>         | 2D/3D DNR  |
| <b>AISLE MODE</b>              | SUPPORTED  |
| <b>SMART IR</b>                | SUPPORTED  |
| <b>MIRROR</b>                  | SUPPORTED  |
| <b>REGION OF INTEREST</b>      | OFF/ON (8 ZONE, RECTANGLE)   |
| <b>MOTION DETECTION</b>        | SUPPORTED  |
| <b>PRIVACY MASKING</b>         | SUPPORTED  |

| SMART FUNCTION               |  |
|------------------------------|--|
| <b>INTELLIGENCE FUNCTION</b> | SUPPORTS FACE, HUMAN, VEHICLE DETECTION  |
| <b>IVS</b>                   | PERIMETER, SINGLE VIRTUAL FENCE, DOUBLE VIRTUAL FENCES, LOITER, CONVERSE, PEOPLE COUNTING                                  |
| AUDIO                        |  |
| <b>COMPRESSION</b>           | G.711, RAW_PCM   |
| <b>BIT RATE</b>              | 8KBPS, 16KPS, 64KBPS   |
| NETWORK                      |  |
| <b>PROTOCOLS</b>             | IPV4/IPV6, 802.1X, HTTP, HTTPS, TCP/IP, UDP/IP, RTSP, DHCP, NTP, RTCP/RTP, PPPOE, SMTP, DNS, UPNP, FTP, ARP, SNMP, TLS/SSL |
| <b>INTEROPERABILITY</b>      | ONVIF, SDK, CGI  |
| <b>STREAMING METHOD</b>      | UNICAST  |
| <b>MAX. USER ACCESS</b>      | 10 USERS   |
| <b>WEB VIEWER</b>            | <IE11, CHROME, FIREFOX, MICROSOFT EDGE   |
| <b>MANAGEMENT SOFTWARE</b>   | CAPTURE ADV  |
| INTERFACE                    |  |
| <b>ETHERNET</b>              | 1 ETHERNET (10/100 BASE-T) RJ-45 CONNECTOR   |
| <b>AUDIO</b>                 | 1 CH INPUT, 1 CH OUTPUT , BUILT-IN MICROPHONE  |
| <b>ALARM</b>                 | 1CH INPUT, 1CH OUTPUT  |
| <b>RESET BUTTON</b>          | SUPPORTED  |
| <b>STORAGE</b>               | BUILT-IN MICRO SD SLOT, UP TO 256G   |
| ELECTRICAL                   |  |
| <b>POWER SUPPLY</b>          | DC12V/POE (IEEE 802.3AF)   |
| <b>POWER CONSUMPTION</b>     | MAX 7.5 W  |
| <b>OPERATING TEMPERATURE</b> | -40°C - 55°C (-40°F - 131°F )  |
| <b>OPERATING HUMIDITY</b>    | LESS THAN 90% RH   |
| <b>INGRESS PROTECTION</b>    | IP66   |
| <b>CERTIFICATIONS</b>        | CE/FCC   |
| <b>CASING</b>                | METAL + PLASTIC  |
| <b>DIMENSIONS</b>            | Φ140×119.2 MM (5.51×4.69 ")  |
| <b>NET WEIGHT</b>            | 0.9 KG (1.98 LB)   |

**FOR MORE INFORMATION,  
CONTACT YOUR ADI SALES PERSON.**