

2 MP HD IR Fixed Bullet



Multi Format: CVI, TVI, AHD, CVBS

The R2-HD2MPBUL2 is a 2MP (1920x1080) bullet camera constructed with a 2.8mm lens. This 2MP Camera is IP66 rated, provides HD Image quality and is ideal for a wide range of indoor/outdoor applications such as commercial applications.

FEATURES

- 2.8MM LENS
- CVI, TVI, AHD, CVBS
- IR DISTANCE: 20M/66 FT
- UTC AND JOYSTICK CONTROLLABLE OSD
- IP66, 12VDC
- WARRANTY: 36 MONTHS
- PART #: R2-HD2MPBUL2
- UPC: 840049306691
- LENGTH: 7.22"
- WIDTH: 2.57"
- HEIGHT: 2.3"
- WEIGHT: 0.64 LB



FOR MORE INFORMATION, CONTACT YOUR ADI SALES PERSON.

Caméra ogivale fixe HD IR 2 Mpx

Multiformat: CVI, TVI, AHD, CVBS



Le modèle R2-HD2MPBUL2 est une caméra ogivale 2 Mpx (1920x1080) dotée d'un objectif 2,8 mm. Elle est homo-loguée IP66, offre une qualité d'image HD et convient à une vaste gamme d'applications intérieures ou extérieures.

CARACTÉRISTIQUES

- OBJECTIF DE 2,8 MM
- CVI, TVI, AHD, CVBS
- DISTANCE (IR) : 20 M/66 PI
- COMMANDE D'AFFICHAGE À L'ÉCRAN DE TYPE MANETTE ET UTC
- IP66, 12VCC
- GARANTIE : 36 MOIS
- PART # : R2-HD2MPBUL2
- UPC : 840049306691
- LONGUEUR : 7,22 PO
- LARGEUR : 2,57 PO
- HAUTEUR : 2,3 PO
- POIDS : 0,64 PI



CAMERA	
IMAGE SENSOR	1/2.9" PROGRESSIVE SCAN CMOS
EFFECTIVE PIXELS	1920(H) x 1080(V)
SCANNING SYSTEM	PROGRESSIVE
ELECTRONIC SHUTTER	AUTO, PAL:1/50-1/10000S, NTSC:1/60-1/10000S
MIN. ILLUMINATION	COLOR: 0.01LUX @ (F1.2,AGC ON); B/W: 0LUX @ (IR LED ON)
S/N RATIO	MORE THAN 48DB
IR RANGE	UP TO 20M
IR ON/OFF CONTROL	AUTO/MANUAL
IR LEDES	2PCS
OSD JOYSTICK	SUPPORTED
UP THE COAX	SUPPORTED
PAN/TILT/ROTATION RANGE	PAN: 0°-360°; TILT: 0°-90°; ROTATION: 0°-360°
LENS	
LENS TYPE	FIXED
IRIS	FIXED IRIS
FOCAL LENGTH	2.8MM
F NUMBER	F2.0
ANGLE OF VIEW	H: 105.2°, V: 56.8°
FOCUS CONTROL	FIXED

VIDEO	
RESOLUTION	1080P (1920x1080)
FRAME RATE	PAL: 25FPS, NTSC: 30FPS
VIDEO OUTPUT	SUPPORT AHD/TVI/CVI/CVBS OUTPUT
DAY/NIGHT	EXT/AUTO/COLOR/MONO
OSD MENU	SUPPORT
WIDE DYNAMIC RANGE	DWDR, OFF/ON
NOISE REDUCTION	3D DNR, AUTO/MANUAL (0-10)
MIRROR	N/A
MOTION DETECTION	SUPPORTED
PRIVACY MASKING	SUPPORTED
GENERAL	
POWER SUPPLY	DC12V±10%
POWER CONSUMPTION	MAX. 5W (12V DC, IR ON)
OPERATING TEMPERATURE	-10°C ~ 55°C (14°F ~ 131°F)
OPERATING HUMIDITY	LESS THAN 85% RH
INGRESS PROTECTION	IP66
CERTIFICATIONS	CE/FCC
CASING	METAL
DIMENSIONS	183.4 x 65.2 x 58.5MM (7.22 x 2.57 x 2.3")
NET WEIGHT	0.29KG (0.64 LB)

FOR MORE INFORMATION,
CONTACT YOUR ADI SALES PERSON.