

5MP HD IR Fixed Bullet



Multi Format: CVI, TVI, AHD, CVBS

The R2-HD5MPBLT is a 5MP (2560 x 1920) bullet camera constructed with a 2.8mm lens. This 5MP Camera is IP66 rated, provides HD Image quality and is ideal for a wide range of indoor/outdoor applications such as commercial applications.

FEATURES

- 2.8MM LENS
- CVI, TVI, AHD, CVBS
- IR DISTANCE: 20M/66FT
- UTC & JOYSTICK CONTROLLABLE OSD
- IP66, 12VDC
- WARRANTY: 36 MONTHS
- R2-HD5MPBLT
- UPC: 840049305410
- LENGTH: 7.39"
- WIDTH: 2.52"
- HEIGHT: 2.52"
- WEIGHT: 1.08 LB



Caméra Ogivale Fixe HD IR 5 Mpx



Multiformat : CVI, TVI, AHD, CVBS

Le modèle R2-HD5MPBLT est une caméra ogivale 5 Mpx (2560 x 1920) dotée d'un objectif 2,8 mm. Elle est homo-loguée IP66, offre une qualité d'image HD et convient à une vaste gamme d'applications intérieures ou extérieures.

FEATURES

- OBJECTIF DE 2,8 MM
- CVI, TVI, AHD, CVBS
- DISTANCE (IR) : 20 M/66 PI
- COMMANDE D’AFFICHAGE À L’ÉCRAN DE TYPE MANETTE ET UTC
- IP66, 12 VCC
- GARANTIE : 36 MOIS
- R2-HD5MPBLT
- UPC: 840049305410
- LENGTH: 7.39"
- WIDTH: 2.52"
- HEIGHT: 2.52"
- WEIGHT: 1.08 LB



CAMERA	
IMAGE SENSOR	1/3" PROGRESSIVE SCAN CMOS
EFFECTIVE PIXELS	2560(H) x 1920(V)
ELECTRONIC SHUTTER	AUTO, PAL: 1/25-1/10000S, NTSC: 1/30-1/10000S
MIN. ILLUMINATION	Color: 0.05Lux@(F1.2,AGC ON) ; B/W: 0Lux@(IR LED ON)
S/N RATIO	MORE THAN 48DB
IR RANGE	UP TO 20 M
IR LEDES	24PCS
OSD JOYSTICK	SUPPORTED
UP THE COAX	SUPPORTED
PAN/TILT/ROTATION RANGE	PAN:0°-360°, TILT:0°-90°, ROTATION:0°-360°
LENS	
LENS TYPE	FIXED FOCUS
IRIS	FIXED IRIS
FOCAL LENGTH	2.8MM
F NUMBER	F2.0
ANGLE OF VIEW	H: 92.3°, V: 50.8°
VIDEO	
RESOLUTION	5MP (2560x1920)
FRAME RATE	20FPS
VIDEO OUTPUT	SUPPORT AHD/TVI/CVI/CVBS OUTPUT
DAY/NIGHT	Ext / AUTO / Color / B/W
OSD MENU	SUPPORTED

WIDE DYNAMIC RANGE	DWDR, OFF/ON
GAIN CONTROL	AUTO
NOISE REDUCTION	2D DNR, MANUAL(1-16)
WHITE BALANCE	AUTO
BLC	SUPPORTED
GENERAL	
POWER SUPPLY	DC12V ±10%
POWER CONSUMPTION	MAX. 4W (12V DC, IR ON)
OPERATING TEMPERATURE	-10 °C ~ 55 °C (14°F ~ 131 °F)
OPERATING HUMIDITY	LESS THAN 85% RH
INGRESS PROTECTION	IP66
CERTIFICATIONS	CE/FCC
CASING	METAL
POWER SUPPLY	DC12V/2A
DIMENSIONS	187.6 × 64 × 64 MM (7.39"x2.52"x2.52")
NET WEIGHT	0.49 KG (1.08 LB)

FOR MORE INFORMATION,
CONTACT YOUR ADI SALES PERSON.