

# 5 MP HD IR Fixed Eyeball



Multi Format: CVI, TVI, AHD, CVBS

The R2-HD5MPEYE is a 5MP (2560 x 1920) eyeball camera constructed with a 2.8mm lens. This 5MP Camera is IP66 rated, provides HD Image quality and is ideal for a wide range of indoor/outdoor applications.

## FEATURES

- 2.8MM LENS
- CVI, TVI, AHD, CVBS
- IR DISTANCE: 20M/66FT
- UTC & JOYSTICK CONTROLLABLE OSD
- IP66, 12VDC
- WARRANTY: 36 MONTHS
- PART #: R2-HD5MPEYE
- UPC: 840049305366
- DIMENSION:  $\Phi 94 \times 84\text{MM}$ (3.7  $\times$  3.3")
- WEIGHT: 0.79 LB



FOR MORE INFORMATION, CONTACT YOUR ADI SALES PERSON.



# Caméra Sphérique Fixe HD IR 5 Mpx

Multiformat: CVI, TVI, AHD, CVBS

Le modèle R2-HD5MPEYE est une caméra sphérique 5 Mpx (2560 x 1920) dotée d'un objectif 2,8 mm. Elle est homologuée IP66, offre une qualité d'image HD et convient à une vaste gamme d'applications intérieures ou extérieures.

## FEATURES

- OBJECTIF DE 2,8 MM
- CVI, TVI, AHD, CVBS IR
- DISTANCE (IR) : 20 M/66 PI
- COMMANDE D'AFFICHAGE À L'ÉCRAN DE TYPE MANETTE ET UTC
- IP66, 12VCC
- GARANTIE : 36 MOIS
- PART #: R2-HD5MPEYE
- UPC: 840049305366
- DIMENSION:  $\Phi 94 \times 84$ MM(3.7  $\times$  3.3")
- WEIGHT: 0.79 LB



CAMERA	
<b>IMAGE SENSOR</b>	1/3" PROGRESSIVE SCAN CMOS
<b>EFFECTIVE PIXELS</b>	2560(H) x 1920(V)
<b>SCANNING SYSTEM</b>	PROGRESSIVE
<b>ELECTRONIC SHUTTER</b>	AUTO/MANUAL, PAL:1/25-1/10000S, NTSC:1/30-1/10000S
<b>MIN. ILLUMINATION</b>	COLOR:0.05LUX@(F1.2,AGC ON) ; B/W:0LUX@(IR LED ON)
<b>S/N RATIO</b>	MORE THAN 48DB
<b>IR RANGE</b>	UP TO 20M
<b>IR ON/OFF CONTROL</b>	AUTO/MANUAL
<b>IR LEDES</b>	18PCS
<b>OSD JOYSTICK</b>	SUPPORTED
<b>UP THE COAX</b>	SUPPORTED
<b>PAN/TILT/ROTATION RANGE</b>	PAN:0°-360°; TILT:0°-90°; ROTATION:0°-360°
LENS	
<b>LENS TYPE</b>	FIXED
<b>IRIS</b>	FIXED IRIS
<b>FOCAL LENGTH</b>	2.8MM
<b>F NUMBER</b>	F2.0
<b>ANGLE OF VIEW</b>	H: 92.3°, V: 50.8°
<b>FOCUS CONTROL</b>	FIXED

VIDEO	
<b>RESOLUTION</b>	5MP (2560×1920)
<b>FRAME RATE</b>	PAL:20FPS ,NTSC:20FPS
<b>DAY/NIGHT</b>	EXT /AUTO /COLOR/MONO
<b>OSD MENU</b>	SUPPORTED
<b>WIDE DYNAMIC RANGE</b>	DWDR, OFF/ON
<b>NOISE REDUCTION</b>	2D DNR(MANUAL): 1-16
<b>White Balance</b>	Auto
<b>BLC</b>	SUPPORTED
<b>MIRROR</b>	SUPPORTED
GENERAL	
<b>POWER SUPPLY</b>	DC12V±10%
<b>POWER CONSUMPTION</b>	MAX. 4W (12V DC, IR ON)
<b>OPERATING TEMPERATURE</b>	-10 °C - 55 °C (14°F - 131 °F)
<b>OPERATING HUMIDITY</b>	LESS THAN 85% RH
<b>INGRESS PROTECTION</b>	IP66
<b>CERTIFICATIONS</b>	CE/FCC
<b>CASING</b>	METAL
<b>DIMENSIONS</b>	Φ94×84MM (3.7×3.3")
<b>NET WEIGHT</b>	0.36KG (0.79LB)

FOR MORE INFORMATION,  
CONTACT YOUR ADI SALES PERSON.