

5MP HD IR Motorized Dome

Multi Format: CVI, TVI, AHD, CVBS



The R2-HD5MPMODM is a 5MP (2560 x 1920) dome camera constructed with a 2.8-12mm lens. This 5MP Camera is IP66 rated, provides HD Image quality and is ideal for a wide range of indoor/outdoor applications.

FEATURES

- 2.8-12MM LENS
- CVI, TVI, AHD, CVBS
- IR DISTANCE: 30M/98FT
- UTC & JOYSTICK CONTROLLABLE OSD
- IP66/IK10, 12VDC
- WARRANTY: 36 MONTHS
- PART #: R2-HD5MPMODM
- UPC: 840049305397
- DIMENSION: Φ 5.12" x 4.41"
- WEIGHT: 1.48 LB



Caméra Dôme Motorisée HD IR 5 Mpx



Multiformat : CVI, TVI, AHD, CVBS

Le modèle R2-HD5MPMODM est une caméra dôme 5 Mpx (2560 x 1920) dotée d'un objectif 2,8 - 12mm. Elle est homo-loguée IP66, offre une qualité d'image HD et convient à une vaste gamme d'applications intérieures ou extérieures.

FEATURES

- OBJECTIF DE 2,8 - 12 MM
- CVI, TVI, AHD, CVBS
- DISTANCE (IR) : 30 M/98 PI
- COMMANDE D'AFFICHAGE À L'ÉCRAN DE TYPE MANETTE ET UTC
- IP66/IK10, 12 VCC
- GARANTIE : 36 MOIS
- PART #: R2-HD5MPMODM
- UPC: 840049305397
- DIMENSION: Φ 5.12" x 4.41"
- WEIGHT: 1.48 LB



| CAMERA | |
|--------------------------------|--|
| IMAGE SENSOR | 1/3" PROGRESSIVE SCAN CMOS |
| EFFECTIVE PIXELS | 2560(H) x 1920(V) |
| ELECTRONIC SHUTTER | AUTO, PAL: 1/25-1/10000S, NTSC: 1/30-1/10000S |
| MIN. ILLUMINATION | Color: 0.05Lux@(F1.2,AGC ON) ; B/W: 0Lux@(IR LED ON) |
| S/N RATIO | MORE THAN 48DB |
| IR RANGE | UP TO 30 M |
| IR LEDES | 15PCS |
| OSD JOYSTICK | SUPPORTED |
| UP THE COAX | SUPPORTED |
| PAN/TILT/ROTATION RANGE | Pan:0°-355°; Tilt:0°-80°; Rotation:0°-355° |
| LENS | |
| LENS TYPE | MOTORIZED FOCUS |
| IRIS | FIXED IRIS |
| FOCAL LENGTH | 2.8-12MM |
| F NUMBER | F1.6 |
| ANGLE OF VIEW | H: 88°-37.6°, V: 47.2°-21.1° |
| VIDEO | |
| RESOLUTION | 5MP (2560x1920) |
| FRAME RATE | 20FPS |
| VIDEO OUTPUT | SUPPORT AHD/TVI/CVI/CVBS OUTPUT |
| DAY/NIGHT | Ext / AUTO / Color / B/W |
| OSD MENU | SUPPORTED |

| WIDE DYNAMIC RANGE | DWDR, OFF/ON |
|------------------------------|--------------------------------|
| GAIN CONTROL | AUTO |
| NOISE REDUCTION | 2D DNR, MANUAL(1-16) |
| WHITE BALANCE | AUTO |
| BLC | SUPPORTED |
| GENERAL | |
| POWER SUPPLY | DC12V ±10% |
| POWER CONSUMPTION | MAX. 4.5W (12V DC, IR ON) |
| OPERATING TEMPERATURE | -10 °C ~ 55 °C (14°F ~ 131 °F) |
| OPERATING HUMIDITY | LESS THAN 85% RH |
| INGRESS PROTECTION | IP66, IK10 |
| CERTIFICATIONS | CE/FCC |
| CASING | METAL |
| DIMENSIONS | Φ130 x 112 MM (5.12" x 4.41") |
| NET WEIGHT | 0.67 KG (1.48 LB) |

FOR MORE INFORMATION,
CONTACT YOUR ADI SALES PERSON.