

4CH HD Digital Video Recorder



H.265 2TB HDD - CVI, TVI, AHD, CVBS & IP

The R2-HDDVR4C2T is a 4 channel H.265 HD Digital Video Recorder (2TB) that offers flexibility to connect HD Multi-Format and Network cameras. This new generation DVR is widely applied in the areas of public security, education, communication, transportation, military, finance/banking and various other installation applications.

FEATURES

- SUPPORTS AHD, TVI, CVI, CVBS, IP VIDEO INPUTS
- MAX. 6CH IP CAMERA INPUTS, EACH CHANNEL UP TO 5MP
- UP TO 5MP RESOLUTION RECORDING
- SUPPORTS HDMI AND VGA OUTPUT
- SMART SEARCH & PLAYBACK
- SUPPORTS ONE HDD UP TO 8TB
- 2TB HDD INCLUDED
- WARRANTY: 36 MONTHS
- PART #: R2-HDDVR4C2T
- UPC: 840049305465
- LENGTH: 10.04"
- WIDTH: 9.61"
- HEIGHT: 1.73"
- WEIGHT: 1.98 LB (w/o HDD)



FOR MORE INFORMATION, CONTACT YOUR ADI SALES PERSON.

Enregistreur Vidéo Numérique 4 Canaux



Disque HDD H.265 2 To - CVI, TVI,
AHD, CVBS et IP

Le modèle R2-HDDVR4C2T est un enregistreur vidéo numérique 4 canaux H.265 HD (2 To) acceptant plusieurs formats HD et pouvant être connecté à des caméras réseau. Cet enregistreur vidéo de nouvelle génération est couramment utilisé pour la sécurité publique, les écoles, les communications, le transport, les activités militaires, les institutions financières, etc.

FEATURES

- PRISE EN CHARGE DES ENTRÉES VIDÉO AHD, TVI, CVI, CVBS, IP
- MAX. ENTRÉES DE CAMÉRA IP 6 CANAUX, CHACUN JUSQU'À 5MP
- RÉOLUTION D'ENREGISTREMENT JUSQU'À 5 MPX
- PRISE EN CHARGE DES SORTIES HDMI ET VGA
- RECHERCHE ET LECTURE INTELLIGENTES
- PRISE EN CHARGE D'UN DISQUE HDD JUSQU'À 8 TO
- DISQUE HDD DE 2 TO INCLUS
- GARANTIE : 36 MOIS
- PART #: R2-HDDVR4C2T
- UPC: 840049305465
- LENGTH: 10.04"
- WIDTH: 9.61"
- HEIGHT: 1.73"
- WEIGHT: 1.98 LB (w/o HDD)



FOR MORE INFORMATION, CONTACT YOUR ADI SALES PERSON.

VIDEO AND AUDIO	
ANALOG VIDEO INPUT	4-CH BNC
AHD INPUT	5MP, 4MP, 3MP, 1080P, 720P
TVI INPUT	5MP, 4MP, 3MP, 1080P, 720P
CVI INPUT	5MP, 4MP, 3MP, 1080P, 720P
CVBS INPUT	PAL/NTSC
IP VIDEO INPUT	4+2, EACH CHANNEL UP TO 1080P
AUDIO IN/OUT	1/1
TWO-WAY TALK	N/A
HDMI OUTPUT	3840×2160, 1920×1080, 1440×900, 1280×1024
VGA OUTPUT	1920×1080, 1440×900, 1280×1024
CVBS OUTPUT	SUPPORTED
SYNCHRONOUS PLAYBACK	4/1
RECORDING	
ENCODING RESOLUTION	5MP, 4MP, 1080P, 720P, 960H, D1, CIF
FRAME RATE	5MP@6FPS, 4MP@7FPS, 1080P@15FPS
VIDEO BIT RATE	MAIN STREAM: 128KBPS-4096KBPS, SUB STREAM: 16KBPS-1024KBPS
DUAL STREAM	SUPPORTED
NETWORK	
NETWORK INTERFACE	1 RJ45 10M/100M SELF-ADAPTIVE ETHERNET INTERFACE
PROTOCOLS	HTTP, HTTPS, TCP/IP, IPV4, UPNP, UDP, RTSP, SMTP, NTP, DNS, DHCP, P2P, IP FILTER, DDNS, 802.1X, SNMP
REMOTE USERS	4
HARD DISK	
SATA	1 SATA INTERFACES
CAPACITY	UP TO 8TB CAPACITY FOR EACH DISK
INTERFACE	
ALARM IN/OUT	N/A
USB INTERFACE	2 PORTS (USB 2.0 X 2)
GENERAL	
POWER SUPPLY	DC12V/2A
POWER CONSUMPTION	MAX 15W (WITHOUT HDD)
WORKING TEMPERATURE	-10 °C - 50 °C (14 °F - 122 °F)
WORKING HUMIDITY	LESS THAN 90% RH
DIMENSIONS (W×D×H)	255 X 244 X 44 MM (10.04 × 9.61 × 1.73 INCH)
NET WEIGHT	0.9 KG (1.98 LB)

**FOR MORE INFORMATION,
CONTACT YOUR ADI SALES PERSON.**