

# 16CH Network Video Recorder

H.265 4TB - 16CH PoE Ports



The R2-NVR16C4TB is a 16 channel H.265 Network Video Recorder with 4TB hard drive storage which can connect network cameras and provide powerful surveillance. This new generation NVR is widely applied in the areas of public security, education, communication, transportation, military, finance/banking and various other installation applications.

## FEATURES

- UP TO 16CH IP CAMERA ACCESS
- UP TO 8MP RESOLUTION RECORDING
- 16CH POE PORTS
- SMART SEARCHING AND PLAYBACK
- SUPPORTS TWO HDD, EACH UP TO 12TB HDD
- 4TB HDD INCLUDED
- WARRENTY: 36 MONTHS
- PART #: R2-NVR16C4TB
- UPC: 840049305458
- LENGTH: 16.65"
- WIDTH: 12.2"
- HEIGHT: 2.2"
- WEIGHT: 6.05 LB (w/o HDD)



FOR MORE INFORMATION, CONTACT YOUR ADI SALES PERSON.

# Enregistreurs Vidéo Réseau 16 Canaux



H.265 4To - Ports PoE 16 Canaux

Le modèle R2-NVR16C4TB est un reistreur vidéo réseau 16 canaux H.265 avec disque dur de 4 To qui peut se connecter aux caméras réseau et offrir des capacités de surveillance puissantes. Cet enregistreur vidéo de nouvelle génération est couramment utilisé pour la sécurité publique, les écoles, les communications, le transport, les activités militaires, les institu-tions financières, etc.

## FEATURES

- ACCÈS À LA CAMÉRA IP, JUSQU'À 16 CANAUX
- RÉOLUTION D'ENREGISTREMENT JUSQU'À 8 MPX
- PORTS POE 16 CANAUX
- RECHERCHE ET LECTURE INTELLIGENTES
- PRISE EN CHARGE DE DEUX DISQUES HDD DE 12 TO CHACUN
- DISQUE HDD DE 4 TO INCLUS
- GARANTIE : 36 MOIS
- PART #: R2-NVR16C4TB
- UPC: 840049305458
- LENGTH: 16.65"
- WIDTH: 12.2"
- HEIGHT: 2.2"
- WEIGHT: 6.05 LB (w/o HDD)



VIDEO INPUT	
IP CAMERA INPUT	16 CHANNEL
INCOMING BANDWIDTH	112 MBPS
OUTGOING BANDWIDTH	112 MBPS
VIDEO OUTPUT	
HDMI OUTPUT	3840×2160,1920×1080, 1280×1024, 1024×768
VGA OUTPUT	1920×1080, 1280×1024, 1024×768
DECODING CAPACITY	1CH 8MP, 4CH 1080P, 8CH D1, 16CH D1@30FPS
DUAL STREAM	SUPPORTED
MULTI-SCREEN DISPLAY	1/4/8/9/16
RECODING	
RESOLUTION	8MP, 6MP, 5MP, 4MP, 3MP, 1080P, 720P, D1 ETC.
RECORDING MODE	MANUAL, SCHEDULE (REGULAR, CONTINUOUS), EVENT
TRIGGER EVENTS	MOTION DETECTION, VIDEO LOSS, ALARM IN, IVS
PLAYBACK AND BACKUP	
SYNC PLAYBACK	16/9/4/1
SEARCH MODE	TIME /DATE, ALARM, PICTURE GRID, EVENT
BACKUP MODE	USB DEVICE, NETWORK
NETWORK	
INTERFACE	1 RJ-45 PORT (10/100/1000 MBPS)
POE	16 PORTS (IEEE 802.3AF), 128W
NETWORK FUNCTION	HTTP, HTTPS, TCP/IP, IPV4, UPNP, UDP, RTSP, SMTP, NTP, DNS, DHCP, P2P, IP FILTER, DDNS, 802.1X, SNMP, 3G/4G, PPPOE
REMOTE USERS	8 USERS

SMART PHONE	IPHONE, IPAD, ANDROID
INTEROPERABILITY	ONVIF, SDK, CGI
STORAGE	
HDD	2 SATA PORTS, UP TO 12TB FOR EACH HDD
CLOUD STORAGE	SUPPORTED
INTERFACE	
AUDIO I/O	1/1
ALARM INPUT	8CH
ALARM OUTPUT	2CH
USB	3 PORTS (USB 2.0 × 3)
GENERAL	
POWER SUPPLY	AC100 - 240V
POWER CONSUMPTION	< 15 W (WITHOUT HDD)
OPERATING CONDITIONS	-10 °C ~ 50 °C (14 °F ~ 122 °F)
STORAGE CONDITIONS	LESS THAN 90% RH
CERTIFICATIONS	CE/FCC
DIMENSIONS	372 × 310.5 × 46.5 MM (16.65 × 12.2 × 2.2 INCH)
NET WEIGHT	2.75 KG (6.05 LB) WITHOUT HDD

**FOR MORE INFORMATION,  
CONTACT YOUR ADI SALES PERSON.**