

STAINLESS STEEL Drop-In Bar Sinks With Deep Drawn Bowls



Featuring **Deep Drawn**
Seamless Sink Bowls



DBS-1 Shown



DBS-2 Shown



DBS-53C Shown

Item #: _____ Qty #: _____

Model #: _____

Project #: _____

FEATURES:

One piece **Deep Drawn** sink bowls measuring 10" x 14" x 10".
Deck mounted faucet.
Optional embossed and seamless drainboard(s).

MECHANICAL:

Each sink bowl includes 8-9/16" high overflow pipe with 1 1/2" IPS drain.

4" O.C., deck mount faucet

Faucets meet federal lead free standards.

MATERIAL:

20 gauge, 300 stainless steel

OPTIONAL:

A-1: Perforated cover for sink bowl

A-16: Perforated basket for sink bowl

K-316-LU: Add wrist handles

Conforms To NSF 61/9 Lead Free Requirements

	Model #	Faucet Length/Type	# of Drbds.	Drbd. Size	Drainboard Location	Outside Dim. W x L	Cut Out Size W x L	Approx. Weight	Approx. Cu. Ft.
1 COMP.	DBS-1	6" Swing Spout	0	N/A	N/A	13" x 19"	12 1/4" x 18 1/4"	21 lbs.	3
2 COMP.	DBS-2	6" Swing Spout	0	N/A	N/A	25 1/2" x 19"	24 3/4" x 18 1/4"	26 lbs.	4
	DBS-3	12" Swing Spout	0	N/A	N/A	38" x 19"	37 1/4" x 18 1/4"	42 lbs.	9
3 COMP.	DBS-43L	12" Swing Spout	1	12"	Right	21 1/8" x 48 9/16"	17" x 47"	88 lbs.	10
	DBS-43R	12" Swing Spout	1	12"	Left	21 1/8" x 48 9/16"	17" x 47"	88 lbs.	10
	DBS-53C	12" Swing Spout	2	12"	Left & Right	21 1/8" x 60 5/16"	17" x 59"	100 lbs.	21
	DBS-63C	12" Swing Spout	2	18"	Left & Right	21 1/8" x 72 5/16"	17" x 71"	110 lbs.	24


L and R indicate sink location. "C" indicates sink is centered.

WARNING: Equipment that include faucets on this page may contain a chemical known to the State of California to cause cancer, birth defects or other reproductive harm.

DIMENSIONS and SPECIFICATIONS


TOL Overall: ± .500" Interior: ± .250"

ALL DIMENSIONS ARE TYPICAL







DBS-1

Cut-Out Size
12 1/4" x 18 1/4"
1 1/4" radius corners






DBS-2



Cut-Out Size
24 3/4" X 18 1/4"
1 1/4" radius corners




DBS-3




Cut-Out Size
37 1/4" x 18 1/4"
1 1/4" radius corners




DBS-43R



DBS-43L



DBS-53C



DBS-63C

