



WORK TABLE WITH SINK

Galvanized Undershelf & Legs

Conforms To NSF 61/9 Lead Free Requirements



Item #: _____	Qty #: _____
Model #: _____	
Project #: _____	

Rolled Rim Edge on Front & Square Edges on Side & Back



Galvanized Legs w/ Adjustable Plastic Bullet Feet



KLAG-11B-305L-X Shown



FEATURES:

Top is furnished with 1 5/8" sanitary rolled rim on front and square ends, and 5" backsplash at rear.

Three hat-channels stud welded under tabletop to reinforce and maintain a level work surface.

Aluminum die cast "leg-to-shelf" clamp secures shelf to leg eliminating unsightly nuts and bolts. Undershelf is fully adjustable.

MECHANICAL:

K-50 deck mounted lead free compliant faucet included.

Supply is 1/2" hot and cold with faucet holes on 4" centers.

Stainless steel basket drain 1-1/2" IPS

CONSTRUCTION:

All TIG welded. Exposed weld areas polished to match adjacent surface.

Top is sound deadened.

Roll formed embossed galvanized hat channels are secured to top by means of structural adhesive and weld studs.

Gussets welded to support hat channels.

MATERIAL:

TOP: 16 gauge stainless steel type "430" series.

SHELF: 18 gauge galvanized steel.

LEGS: 1 5/8" diameter tubular galvanized steel. Galvanized steel gussets.

1" adjustable plastic bullet feet.

30" WIDE Model #	Length (L)	Sink Location	Approx. Weight	Approx. Cu. Ft.
KLAG-11B-304L-X	48"	Left	130 lbs.	29
KLAG-11B-304R-X	48"	Right	130 lbs.	29
KLAG-11B-305L-X	60"	Left	150 lbs.	35
KLAG-11B-305R-X	60"	Right	150 lbs.	35
KLAG-11B-306L-X	72"	Left	180 lbs.	41
KLAG-11B-306R-X	72"	Right	180 lbs.	41

Choose Left or Right Sink Position

WARNING: Equipment that include faucets on this page may contain a chemical known to the State of California to cause cancer, birth defects or other reproductive harm.



Customer Service Available To Assist You 1-800-645-3166 8:30 am - 7:00 pm E.S.T.

For Orders & Customer Service:

Email: customer@advancetabco.com or Fax: 631-242-6900

For Smart Fabrication™ Quotes:

Email: smartfab@advancetabco.com or Fax: 631-586-2933

DETAILS and SPECIFICATIONS

TOL \pm .500"

ALL DIMENSIONS ARE TYPICAL

