

# End stop limit switch SDK-4-PK-3

Part number: 10033

FESTO



## Data sheet

Feature	Value
Valve function	3/2, closed, monostable
Actuation type	Mechanical
Standard nominal flow rate	16 l/min
Pneumatic working port	PK-3
Operating pressure	0 bar ... 8 bar
Structural design	Ball seat
Reset method	Mechanical spring
Nominal width	0.6 mm
Type code	SDK
Exhaust air function	With flow control option
Sealing principle	Soft
Type of control	Direct
Flow direction	Non-reversible
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Temperature of medium	-10 °C ... 80 °C
Ambient temperature	-10 °C ... 80 °C
Actuating force	17 N
Type of mounting	With through-hole
Pneumatic connection 1	PK-3
Pneumatic connection 2	PK-3
Pneumatic connection 3	Not ducted