

# Barbed bulkhead connector SCN-PK-6

Part number: 11974

FESTO



## Data sheet

Feature	Value
Nominal width	4.8 mm
Type code	SCN
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Ambient temperature	0 °C ... 60 °C
Pneumatic connection 1	for pneumatic tubing outside diameter 8 mm
Note on materials	RoHS-compliant
Housing material	Aluminum
Nut material	Steel, galvanized