

Angled plug socket SIE-WD-TR

Part number: 12956

FESTO



Data sheet

Feature	Value
Type code	SIE
Conforms to standard	EN 61076-2-101 EN 61984
Type of mounting	With union nut
Product weight	13 g
Electrical connection	4-pin Angled socket/screw terminal M12x1
Plug coding	A
DC operating voltage range	0 V ... 250 V
Operating voltage range AC	0 V ... 250 V
Current rating at 40°C	4 A
Surge resistance	2.5 kV
Approved cable diameter	4 mm ... 6 mm
Connection cross section	0.25 mm ² ... 0.75 mm ²
Degree of protection	IP67
Ambient temperature	-25 °C ... 85 °C
CE marking (see declaration of conformity)	As per EU low voltage directive
Note on materials	RoHS-compliant
Contamination level	3
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
Housing material	PA
Housing colour	Transparent
Material of union nut	PA
Material of pin contacts	Brass White bronze, coated