

# Plastic tubing PUN-CM-10-SW

Part number: 130817

FESTO



## Data sheet

Feature	Value
Outside diameter	10 mm
Bending radius relevant for flow rate	60 mm
Inside diameter	7 mm
Min. bending radius	30 mm
Type code	PUN-CM
Tubing characteristics	Suitable for energy chains in applications with high cycle rates
Pneumatic tubing test conditions	Suitability for energy chains: >5 million cycles as per FN 942021
Temperature-dependent operating pressure	-0.95 bar ... 10 bar
Surface resistance	0.01 MOhm ... 10 MOhm
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Ambient temperature	-35 °C ... 60 °C
Product weight by length	0.0544 kg/m
Pneumatic connection	For plug connection outside diameter 10 mm
Color	Black
Shore hardness	D 52 +/-3
Note on materials	Free of copper and PTFE
Material of pneumatic tubing	TPE-U(PU)