

Cartridge QSPKG14-5/16-U

Part number: 132933

FESTO



Data sheet

Feature	Value
Size	Standard
Nominal width	5.2 mm
Type code	QSPKG
Mounting position	Any
Pack size	10
Structural design	Push-pull principle
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Maritime classification	See certificate
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-5 °C ... 60 °C
Product weight	5.3 g
Pneumatic connection 1	QSP...14
Pneumatic connection 2	for pneumatic tubing outside diameter 5/16"
Releasing ring color	Gray
Note on materials	RoHS-compliant
Housing material	PA-reinforced
Releasing ring material	POM
Material of tubing seal	NBR
Material of tube retaining claw	High-alloy stainless steel