

# Cartridge QSPLKG18-3/8-U

Part number: 132949

FESTO



## Data sheet

| Feature   | Value   |
|---|---|
| Size  | Standard                                      |
| Nominal width                                   | 6.5 mm  |
| Type code                                       | QSPLKG  |
| Mounting position                               | Any   |
| Pack size                                       | 10  |
| Structural design                               | Push-pull principle                           |
| Operating pressure for entire temperature range | -0.95 bar ... 10 bar                          |
| Maritime classification                         | See certificate                               |
| Operating medium                                | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media        | Operation with oil lubrication possible       |
| Corrosion resistance class (CRC)                | 1 - Low corrosion stress                      |
| Ambient temperature                             | -5 °C ... 60 °C                               |
| Product weight                                  | 10.9 g  |
| Pneumatic connection 1                          | QSP...18                                      |
| Pneumatic connection 2                          | for pneumatic tubing outside diameter 3/8"    |
| Releasing ring color                            | Gray  |
| Note on materials                               | RoHS-compliant                                |
| Housing material                                | PA-reinforced                                 |
| Releasing ring material                         | POM   |
| Material of tubing seal                         | NBR   |
| Material of tube retaining claw                 | High-alloy stainless steel                    |