

Rod clevis CRSG-M10X1,25

Part number: 13569

FESTO



Data sheet

Feature	Value
Size	M10x1.25
Type code	CRSG
Mounting position	Any
Based on norm	DIN 71752 ISO 8140
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
Ambient temperature	-40 °C ... 150 °C
Product weight	101.8 g
Note on materials	Free of copper and PTFE RoHS-compliant
Bolt material	High-alloy steel
Clevis material	High-alloy steel
Nut material	High-alloy steel
Fuse material	High-alloy steel