


Finger lever valve TH/O-3-PK-3

Part number: 13794

FESTO



Data sheet

| Feature | Value |
|--|--|
| Valve function | 3/2, open/closed, monostable |
| Standard nominal flow rate | 80 l/min |
| Pneumatic working port | PK-3 |
| Operating pressure | 0 bar ... 8 bar |
| Structural design | Piston seat |
| Nominal width | 2.5 mm |
| Type code | TH/O |
| Type of control | Direct |
| Symbol | 00991837 |
| Operating medium | Compressed air as per ISO 8573-1:2010 [:-:-] |
| Ambient temperature | -10 °C ... 60 °C |
| Actuation force in initial position closed | 8 N |
| Actuation force in initial position open | 6 N |
| Product weight | 18 g |
| Type of mounting | With through-hole |
| Pneumatic connection 1 | PK-3 |
| Pneumatic connection 2 | PK-3 |
| Pneumatic connection 3 | PK-3 |
| Seals material | NBR |
| Housing material | Polymer |