



Vacuum suction cup VAS-100-1/4-PUR-B

Part number: 1396098

FESTO



Data sheet

Feature	Value
Suction cup height compensation	3.5 mm
Nominal width	4 mm
Suction cup diameter	100 mm
Suction cup volume	33.5 cm ³
Effective suction cup diameter	90.5 mm
Type code	VAS
Connection position	Top
Mounting position	Any
Symbol	00991485
Suction cup shape	Round, flat
Operating pressure	-0.95 bar ... 0 bar
Nominal operating pressure	-0.7 bar
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-:]
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-20 °C ... 60 °C
Holding force at nominal operating pressure	450 N
Product weight	140 g
Type of mounting	Via vacuum connection
Vacuum connection	G1/4
Color	Blue
Shore hardness	60 +/- 5
Material of screwed trunnion	Die-cast zinc
Note on materials	RoHS-compliant
Suction cup material	PUR