


Cartridge cylinder EGZ-10-15

Part number: 15038

FESTO



Data sheet

Feature	Value
Stroke	15 mm
Piston diameter	10 mm
Type code	EGZ
Cushioning	No cushioning
Mounting position	Any
Mode of operation	Single-acting Pushing
Structural design	Piston Piston rod Cylinder barrel
Position sensing	None
Symbol	00991200
Variants	Piston rod at one end
Operating pressure	1.5 bar ... 8 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-20 °C ... 80 °C
Theoretical force at 6 bar	42 N
Theoretical force at 6 bar, advancing	42 N
Type of mounting	Optionally: With external thread With lock nut
Pneumatic connection	M5
Cover material	POM
Seals material	TPE-U(PU)
Housing material	Brass Nickel-plated
Piston rod material	High-alloy steel