

# Air reservoir CRVZS-0.75

Part number: 160235

FESTO



## Data sheet

Feature	Value
Volume	0.75 l
Type code	CRVZS
Mounting position	Any
Conforms to standard	AD 2000
Symbol	00991528
Operating pressure	-0.095 MPa ... 1.6 MPa
Operating pressure	-0.95 bar ... 16 bar
Operating pressure	-13.78 psi ... 232 psi
Certification	CRN German Technical Control Board (TÜV)
Certificate issuing authority	TSSACRNOH17477.5C
Operating medium	Compressed air as per ISO 8573-1:2010 [-:~:] Nitrogen
Corrosion resistance class (CRC)	3 - High corrosion stress
For use in the food industry	See supplementary material information
Temperature of medium	-10 °C ... 100 °C
Ambient temperature	-10 °C ... 100 °C
Max. tightening torque for connecting thread	23 Nm
Product weight	736 g
Type of mounting	Fixing clips
Pneumatic connection	G1/4
Note on materials	Free of copper and PTFE RoHS-compliant
Air reservoir material	High-alloy stainless steel
Fixing clips material	High-alloy stainless steel