

Sealing ring OL-M10

Part number: 161181

FESTO



Data sheet

Feature	Value
Type code	OL
Based on norm	ISO 16030
Pack size	1
Operating pressure for entire temperature range	-0.95 bar ... 30 bar
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-40 °C ... 100 °C
Manual tightening at RT	yes
Nominal tightening torque	13.5 Nm
Tolerance for nominal tightening torque	± 20%
Note on materials	RoHS-compliant