


# Pneumatic muffler UC-M7

Part number: 161418

FESTO



## Data sheet

Feature	Value
Type code	UC
Mounting position	Any
Pack size	1
Symbol	00991473
Operating pressure	0 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Noise level	58 dB(A)
Ambient temperature	-10 °C ... 70 °C
Product weight	1.2 g
Pneumatic connection	M7
Cushioning insert material	PE
Material of screwed trunnion	PE
Note on materials	RoHS-compliant