



Air solenoid valve MN1H-2-1/2-MS

Part number: 161728

FESTO



Data sheet

Feature	Value
Type code	MN1H
Structural design	Diaphragm valve
Actuation type	Electrical
Sealing principle	Soft
Mounting position	Any
Type of mounting	Line installation
Fitting connection	G1/2
Electrical connection	Form A Plug as per DIN EN 175301-803 Rectangular design
Nominal width	13 mm
Valve function	2/2, closed, monostable
Manual override	Detenting via accessory Non-detenting
Flow direction	Non-reversible
Medium	Filtered compressed air, 200 µm filter mesh
Exhaust air function	Without flow control option
Coil characteristics	110 V AC: 50 Hz, initial power 5.0 VA, holding power 3.7 VA 110 V AC: 60 Hz, initial power 5.0 VA, holding power 3.7 VA 230 V AC: 50 Hz, initial power 5.0 VA, holding power 3.7 VA 230 V AC: 60 Hz, initial power 5.0 VA, holding power 3.7 VA 24 V DC: 2.5 W
Reset method	Pneumatic spring
Type of control	Pilot-controlled
Symbol	00991399
Medium pressure	0.5 bar ... 10 bar
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Standard nominal flow rate	3100 l/min
On switching time	30 ms
Switching time off	100 ms
Housing material	Brass
Material of screws	High-alloy stainless steel
Material number of screw	1.4301
Product weight	400 g

Feature	Value
Degree of protection	IP65 With plug socket