

# Clevis foot CRLNG-40

Part number: 161841

FESTO



## Data sheet

Feature	Value
Size	40
Type code	CRLNG
Based on norm	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Mounting position	Any
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
Ambient temperature	-40 °C ... 80 °C
Product weight	161 g
Note on materials	Free of copper and PTFE RoHS-compliant
Mounting material	Electropolished High-alloy steel
Material of bearing	Polymer