

# Angled plug socket PEV-1/4-WD-LED-230

Part number: 164275

FESTO



## Data sheet

Feature	Value
Type code	PEV
Certification	RCM compliance mark
Switching status indication	LED yellow
Type of mounting	With through-hole
Electrical connection	4-pin Socket, angled
DC operating voltage range	≤180 V
Operating voltage range AC	≤230 V
Current rating	8 A
Degree of protection	IP65
Ambient temperature	-40 °C ... 90 °C
CE marking (see declaration of conformity)	As per EU EMC directive As per EU low voltage directive
Note on materials	RoHS-compliant