

# Elbow click fitting NPKA-L-G18-Q6-P10

Part number: 1655429

FESTO



## Data sheet

Feature	Value
Size	Standard
Nominal width	4 mm
Type code	NPKA
Type of seal on screwed trunnion	Sealing ring
Mounting position	Any
Pack size	10
Structural design	Push-pull principle
Operating pressure	-0.95 bar ... 10 bar
Temperature-dependent operating pressure	-0.95 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Water as per manufacturer's declaration at <a href="http://www.festo.com">www.festo.com</a>
Information on operating and pilot media	Operation with oil lubrication possible
For use in the food industry	See supplementary material information
Ambient temperature	-10 °C ... 60 °C
Max. tightening torque	2 Nm
Nominal tightening torque	1.25 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	7.5 g
Pneumatic connection 1	External thread G1/8
Pneumatic connection 2	for pneumatic tubing outside diameter 6 mm
Note on materials	RoHS-compliant
Housing material	PA66-GF30
Material of threaded seal	PA66-GF30/TPE-U
Sleeve material	POM
Material of tubing seal	NBR