

Plug socket MSSD-C-4P

Part number: 171157

FESTO



Data sheet

Feature	Value
Type code	MSSD
Type of mounting	On air solenoid valve with M3 central screw
Mounting position	Any
Product weight	22 g
Electrical connection	3-pin Socket, angled Form A as per DIN EN 175301-803 Rectangular design MSC Rectangular design MSN1
Cable fitting	Pg9
Cable diameter	6 mm ... 8 mm
Nominal conductor cross section	$\leq 1.5 \text{ mm}^2$
Degree of protection	IP65
Ambient temperature	-25 °C ... 90 °C
Note on materials	RoHS-compliant
Housing material	Polymer
Housing colour	Black