

# Fine filter LFMB-3/8-D-MIDI-NPT

Part number: 173714

FESTO



## Data sheet

Feature	Value
Series	D
Size	Midi
Type code	LFMB
Grade of filtration	1 µm
Condensate drain	Manual, non-detenting
Symbol	00991519
Operating pressure	1 bar ... 16 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [6:8:4] Inert gas
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [5:7:3] Inert gas
Max. standard flow rate for air quality class	1420 l/min
Min. standard flow rate for air quality class	500 l/min
Filter efficiency	99.99 %
Bowl guard	Metal bowl guard
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Temperature of medium	1.5 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Residual oil content	0.5 mg/m <sup>3</sup>
Type of mounting	Optionally: Line installation With mounting bracket
Mounting position	Vertical
Pneumatic connection 1	3/8 NPT
Pneumatic connection 2	3/8 NPT
Housing material	Die-cast zinc
Compressed air filter material	Borosilicate fiber
Material of bowl	PC
Note on materials	Free of copper and PTFE RoHS-compliant