


Clevis flange SNCS-50

Part number: 174399

FESTO



Data sheet

Feature	Value
Size	50
Type code	SNCS
Based on norm	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-40 °C ... 150 °C
Product weight	216 g
Note on materials	RoHS-compliant
Mounting material	Die-cast aluminum
Rod end bearing material	Steel PTFE
Material of screws	Steel Galvanized