

Clevis flange SNCB-32-R3

Part number: 176944

FESTO



Data sheet

| Feature | Value |
|----------------------------------|--|
| Size | 32 |
| Type code | SNCB |
| Based on norm | ISO 15552 |
| Variants | High corrosion protection |
| Corrosion resistance class (CRC) | 3 - High corrosion stress |
| Ambient temperature | -40 °C ... 90 °C |
| Product weight | 100 g |
| Note on materials | Free of copper and PTFE RoHS-compliant |
| Mounting material | Die-cast aluminum With protective coating |
| Bolt material | High-alloy stainless steel |
| Material of bearing | Polymer |
| Disc material | Steel, galvanized |
| Material of screws | High-alloy stainless steel |
| Fuse material | Spring steel, galvanized |