


Clevis flange SNCB-100-R3

Part number: 176949

FESTO



Data sheet

Feature	Value
Size	100
Type code	SNCB
Based on norm	ISO 15552
Variants	High corrosion protection
Corrosion resistance class (CRC)	3 - High corrosion stress
Ambient temperature	-40 °C ... 90 °C
Product weight	986 g
Note on materials	Free of copper and PTFE RoHS-compliant
Mounting material	Die-cast aluminum With protective coating
Bolt material	High-alloy stainless steel
Material of bearing	Polymer
Disc material	Steel, galvanized
Material of screws	High-alloy stainless steel
Fuse material	Spring steel, galvanized