

Low consumption air gun LSP-1/4-C

Part number: 184318

FESTO



Data sheet

Feature	Value
Type code	LSP
Exhaust air function	Metered blowing
Operating pressure	0 bar ... 10 bar
Standard nominal flow rate	120 l/min
Noise level	90 dB(A)
Ambient temperature	-10 °C ... 50 °C
Product weight	125 g
Pneumatic connection	Internal thread G1/4
Housing material	PA6-reinforced