

Connection block CPE10-PRSGO-3

Part number: 187819

FESTO



Data sheet

Feature	Value
Type code	CPE10
Max. no. of valve positions	3
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Product weight	70 g
Sub-base mounting type	With through-hole With H-rail
Pneumatic connection 1	G1/4
Note on materials	Free of copper and PTFE RoHS-compliant
Housing material	PA-reinforced