

Plastic tubing PUN-CM-4-SW

Part number: 188882

FESTO



Data sheet

Feature	Value
Outside diameter	4 mm
Bending radius relevant for flow rate	17 mm
Inside diameter	2.5 mm
Min. bending radius	8 mm
Type code	PUN-CM
Tubing characteristics	Suitable for energy chains in applications with high cycle rates
Pneumatic tubing test conditions	Suitability for energy chains: >5 million cycles as per FN 942021
Temperature-dependent operating pressure	-0.95 bar ... 10 bar
Surface resistance	0.01 MOhm ... 10 MOhm
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Ambient temperature	-35 °C ... 60 °C
Product weight by length	0.0089 kg/m
Pneumatic connection	For plug connection outside diameter 4 mm
Color	Black
Shore hardness	D 52 +/-3
Note on materials	Free of copper and PTFE
Material of pneumatic tubing	TPE-U(PU)