

# Vacuum suction cup holder ESH-HC-4-QS

Part number: 189219

FESTO



## Data sheet

Feature	Value
Suction cup holder height compensator	6 mm
Volume	1.153 cm <sup>3</sup>
Type code	ESH
Mounting position	Vertical
Structural design	Vacuum connection at top with height compensation
Classification of suction cup holder	Size 4
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	0 °C ... 60 °C
Product weight	33 g
Type of mounting	With lock nut
Suction cup mounting	M6
Vacuum connection	QS-6
Note on materials	RoHS-compliant
Seals material	NBR Steel
Retaining bracket material	Aluminum Tempered steel High-alloy steel Brass, nickel-plated POM