


# Pneumatic muffler UOS-1-LF

Part number: 1901207

FESTO



## Data sheet

Feature	Value
Type code	UOS-1-LF
Type of seal on screwed trunnion	without seal
Mounting position	Any
Structural design	Pneumatic muffler, open
Symbol	00992064
Operating pressure	0 MPa ... 0.1 MPa
Operating pressure	0 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [-:--]
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-10 °C ... 50 °C
Type of mounting	With external thread
Product weight	157.9 g
Pneumatic connection	G1
Cushioning insert material	PE
Note on materials	Free of copper and PTFE RoHS-compliant
Housing material	Wrought aluminum alloy