

Push-in L-connector QSML-3/16H-1/8-U

Part number: 190626

FESTO



Data sheet

| Feature | Value |
|-------------------------------------------------|-----------------------------------------------|
| Size | Mini |
| Nominal width | 1.7 mm |
| Type code | QSML |
| Mounting position | Any |
| Pack size | 1 |
| Structural design | Push-pull principle |
| Operating pressure for entire temperature range | -0.95 bar ... 10 bar |
| Maritime classification | See certificate |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media | Operation with oil lubrication possible |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 1.8 g |
| Pneumatic connection 1 | Push-in sleeve QS-3/16" |
| Pneumatic connection 2 | for pneumatic tubing outside diameter 1/8" |
| Releasing ring color | Gray |
| Note on materials | RoHS-compliant |
| Housing material | PBT |
| Releasing ring material | POM |
| Material of tubing seal | NBR |
| Material of tube retaining claw | High-alloy stainless steel |