

Blanking plug QSC-5/8H-U

Part number: 190640

FESTO



Data sheet

Feature	Value
Type code	QSC
Mounting position	Any
Pack size	1
Structural design	Push-pull principle
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Maritime classification	See certificate
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Product weight	4 g
Pneumatic connection 1	Push-in sleeve QS-5/8"
Releasing ring color	Gray
Note on materials	RoHS-compliant
Housing material	PBT