

# Push-in L-fitting QSLV-1/4-5/16-I-U

Part number: 190758

FESTO



## Data sheet

Feature	Value
Size	Standard
Nominal width	4 mm
Type code	QSLV
Type of seal on screwed trunnion	Coating
Mounting position	Any
Pack size	1
Structural design	Push-pull principle
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Maritime classification	See certificate
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Max. tightening torque	14 Nm
Product weight	28 g
Pneumatic connection 1	external thread 1/4 NPT
Pneumatic connection 2	for pneumatic tubing outside diameter 5/16"
Releasing ring color	Gray
Note on materials	RoHS-compliant
Housing material	PBT
Releasing ring material	POM
Material of tubing seal	NBR
Material of tube retaining claw	High-alloy stainless steel