

Multiple distributor QSLV6-1/2-1/2-U

Part number: 190811

FESTO



Data sheet

Feature	Value
Size	Standard
Nominal width	6.5 mm
Type code	QSLV6
Type of seal on screwed trunnion	Coating
Mounting position	Any
Structural design	Push-pull principle
Pack size	1
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Maritime classification	See certificate
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Max. tightening torque	30 Nm
Product weight	211 g
No. of outlets	6
No. of supply lines	1
Pneumatic connection 1	external thread 1/2 NPT
Pneumatic connection 2	for pneumatic tubing outside diameter 1/2"
Releasing ring color	Gray
Material of screwed trunnion	Brass, nickel-plated
Note on materials	RoHS-compliant
Housing material	PBT
Releasing ring material	POM
Material of tubing seal	NBR
Material of tube retaining claw	High-alloy stainless steel