

Push-in T-fitting QSTF-1/2-1/2-U

Part number: 190833

FESTO



Data sheet

| Feature | Value |
|---|--|
| Size | Standard |
| Nominal width | 10 mm |
| Type code | QSTF |
| Type of seal on screwed trunnion | Coating |
| Mounting position | Any |
| Pack size | 1 |
| Structural design | Push-pull principle |
| Operating pressure for entire temperature range | -0.95 bar ... 10 bar |
| Maritime classification | See certificate |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media | Operation with oil lubrication possible |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| Ambient temperature | -10 °C ... 60 °C |
| Max. tightening torque | 30 Nm |
| Product weight | 117 g |
| No. of outlets | 2 |
| No. of supply lines | 1 |
| Pneumatic connection 1 | external thread 1/2 NPT internal thread 1/2 NPT |
| Pneumatic connection 2 | for pneumatic tubing outside diameter 1/2" |
| Releasing ring color | Gray |
| Note on materials | RoHS-compliant |
| Housing material | PBT |
| Releasing ring material | POM |
| Material of tubing seal | NBR |
| Material of tube retaining claw | High-alloy stainless steel |