

Illuminating seal MF-LD-12-24DC

Part number: 19143

FESTO



Data sheet

Feature	Value
Type code	MF-LD
Switching position indication	LED
Type of mounting	On air solenoid valve with M3 central screw
Product weight	1.6 g
Electrical connection	Rectangular design MSF
DC operating voltage range	12 V ... 24 V
Protective earth connection	Available
Nominal power luminous seal	0.05 W
Degree of protection	IP65
Ambient temperature	-25 °C ... 85 °C
Housing material	TPE-U(PU)