


Compressed air filter LF-D-MINI

Part number: 192551

FESTO



Data sheet

| Feature | Value |
|----------------------------------|--|
| Size | Mini |
| Type code | LF |
| Series | D |
| Mounting position | Vertical +/- 5° |
| Grade of filtration | 40 µm |
| Condensate drain | Manually rotating |
| Structural design | Sinter filter with centrifugal separator |
| Max. condensate volume | 22 ml |
| Bowl guard | Metal bowl guard |
| Symbol | 00991519 |
| Operating pressure | 0 bar ... 16 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [-:9:-] Inert gas |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Storage temperature | -10 °C ... 60 °C |
| Air quality class at the output | Compressed air as per ISO 8573-1:2010 [7:8:4] Inert gas |
| Temperature of medium | -10 °C ... 60 °C |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 250 g |
| Type of mounting | Line installation With accessories |
| Pneumatic connection 1 | Sub-base |
| Pneumatic connection 2 | Sub-base |
| Note on materials | RoHS-compliant |
| Compressed air filter material | PE |
| Housing material | Die-cast zinc |
| Material of bowl | PC |